

ARK-8500 Auto Ref-Keratometer



Adjustable LCD Touch Screen



High brightness and contrast 9" wide color TFT LCD screen, smooth touch mode, different angle can be adjusted

Motorized Chin Rest Screen





By pressing the Up & Down buttons, the users can set and adjust the height of the patient's chin freely and quickly

Data Record



3 groups of data stored each measurement, maximum 10 groups of data can be stored

UP/down Auto Tracking



Measure peripheral keratometry precision of eyes with contact lenses fitting

Operation Interface Function



Intuitive icons provide the user an easier operating circumstances, and make the measurement become more convenient and the data to be measured more accurate and fast

Hartmann Imaging Processing Technology

